
Planar[®] T* f/2 - 100 mm



CONTAX[®]/YASHICA[®] mount

A high-speed lens with superb image quality. The demand for a focal length of 100 mm is growing because of its many fields of application: portraiture work, snapshots, architectural and landscape photography.

10 21 58

With its relative aperture of 1:2, the new Zeiss lens permits short shutter speeds to be used even in bad lighting conditions. The low depth of field resulting at full aperture can be employed as an interesting means of picture composition.

Cat. No. of lens:

Number of elements: Number of groups: Max. aperture: Focal length: Negative size: Angular field 2w: Mount:

Aperture scale:

Filter connection:

6 5 f/2 99.9 mm 24 x 36 mm 24° focusing mount with bayonet; TTL metering either at full aperture or in stopped-down position. Aperture priority/Shutter priority/ Automatic programs (Multi-Mode Operation) 2 - 2.8 - 4 - 5.6 - 8 - 11 - 16 - 22 clip-on filter, diameter 70 mm screw thread M 67 x 0.75

Weight:	approx. 670 g
Focusing range:	∞ to 1 m
Entrance pupil:	
Position:	59.0 mm behind first lens vertex
Diameter:	50.0 mm
Exit pupil:	
Position:	32.8 mm in front of the last lens vertex
Diameter:	46.9 mm
Position of principal planes:	
H:	48.8 mm behind first lens vertex
H':	42.0 mm in front of last lens vertex
Back focal distance:	57.9 mm
Distance between first an	d
last lens vertex:	67.7 mm



Performance data: **Planar**[®] T* f/2 - 100 mm Cat. No. 10 21 58

1. MTF Diagrams

The image height u - calculated from the image center - is entered in mm on the horizontal axis of the graph. The modulation transfer T (MTF = Modulation Transfer Factor) is entered on the vertical axis. Parameters of the graph are the spatial frequencies R in cycles (line pairs) per mm given at the top of this page. The lowest spatial frequency corresponds to the upper pair of curves, the highest spatial frequency to the lower pair. Above each graph, the f-number k is given for which the measurement was made. "White" light means that the measurement was made with a subject illumination having the approximate

spectral distribution of daylight. Unless otherwise indicated, the performance data refer to large object distances, for which normal photographic lenses are primarily used.

2. Relative illuminance

In this diagram the horizontal axis gives the image height u in mm and the vertical axis the relative illuminance E, both for full aperture and a moderately stopped-down lens. The values for E are determined taking into account vignetting and natural light decrease.

3. Distortion

Here again the image height u is entered on the horizontal axis in mm. The vertical axis gives the distortion V in % of the relevant image height. A positive value for V means that the actual image point is further from the image center than with perfectly distortion-free imaging (pincushion distortion); a negative V indicates barrel distortion.

> Carl Zeiss Photoobjektive D-73446 Oberkochen

Telephone (07364) 20-6175 Fax (07364) 20-4045 eMail: photo@zeiss.de http://www.zeiss.de

ZEISS

Subject to change.

Modulation transfer T as a function of image height u. Slit orientation: tangential — — — sagittal White light. Spatial frequencies R = 10, 20 and 40 cycles/mm

